



Change the way you think about cleaning



faster



cleaner



greener



safer



better



PORTFOLIO

Spread the joy...
not the dirt



about us

Led by Innovation

Our revolutionary product range helps to transform cleaning times and results, guided by our core values:



INQUIRE

To revolutionise the industry, we speak to users, tailoring our products to meet specific demands.




INNOVATE

Designed with innovation as the primary goal, our class-leading products offer a true four-dimensional clean.



INSPIRE

Our job isn't done until we see how products are transforming businesses and inspiring clients first-hand.



i-team[®]

DANMARK

We believe effective cleaning is more than “just” the removal of soil. It means ensuring the HEALTH and safety of people, while making the job easier, simpler, more efficient and even fun.

It means consistent results all over the world, while protecting the world. And it means creating partnerships to grow our global force for better cleaning.

After all, it takes a team.

The i-team.



JESPER KOCH

Area sales manager
jesper@i-teamdanmark.dk
+45 4020 0164



KRISTINE ELVERDAM

Area sales manager
kristine@i-teamdanmark.dk
+45 2270 4020



MARTIN KRISTENSEN

Area sales manager
martin@i-teamdanmark.dk
+45 5239 3075



NIELS MOESGAARD

Sales & service manager
niels@i-teamdanmark.dk
+45 4117 2233



BRIAN BÆKKE

Ambassador / Business Manager
brian@i-teamglobal.com
+45 6127 5929



JENS GULDBERG

Service i-team Danmark
service@i-teamdanmark.dk

i-team

OFFICE DENMARK & INSPIRATION CENTER

Bygmarken 2B, 3650 Ølstykke
hej@i-teamdanmark.dk
+45 5079 2020





fundamentals



faster



cleaner



greener



safer



better

The i-team approach ensures that each of our products are built with our five fundamentals in mind, providing you with more effective tools that reduce cleaning times, improve cleaning outcomes - all while optimising safety and environmental considerations.

contents

i-team Catalogue **02**

| | |
|--------------|-----------|
| About us | 03 |
| Fundamentals | 06 |
| Contents | 07 |
| Made Blue | 08 |
| Segments | 09 |

Commercial Floor Cleaning **10**

| | |
|----------------------------|-----------|
| i-mop family | 12 |
| Join the revolution | 14 |
| imop Lite & accessories | 16 |
| i-mop XL | 18 |
| i-mop XXL | 20 |
| i-mop XL & XXL accessories | 22 |
| i-dose concept | 24 |
| i-link | 25 |
| i-scrub 30EM Pro | 26 |
| i-scrub 21B | 28 |
| i-remove | 30 |
| i-drive | 32 |

Commercial Vacuum Cleaning **34**

| | |
|----------------------|-----------|
| i-vac 5 | 36 |
| i-vac 5B | 38 |
| i-vac 6 | 40 |
| i-vac 9B | 42 |
| co-botic 1700 basic | 44 |
| co-botic 1700 Hotel | 45 |
| co-botic accessories | 46 |
| i-move 2.5B | 47 |

Surface Cleaning **48**

| | |
|-------------|-----------|
| i-spraywash | 50 |
| i-scrub 26H | 53 |
| i-fibre | 54 |

Air Purification **56**

| | |
|--------------|-----------|
| i-air Pro | 58 |
| i-sense | 59 |
| i-fogger 3.5 | 60 |
| 4D cleaning | 61 |

Cleaning Equipment & Accessories **62**

| | |
|----------------------------|-----------|
| i-land S | 64 |
| i-land L Pro | 65 |
| i-land L Pro Drive | 66 |
| i-land XL Pro | 67 |
| i-power | 68 |
| i-stack & i-charge | 69 |
| i-matt | 70 |
| i-dose | 71 |
| i-suit | 72 |
| i-store / i-wall / i-stand | 73 |
| i-know | 74 |
| Partner network | 75 |



made blue

At i-team, we believe that we have a responsibility to improve our environmental outcomes.


Cleaning is a water-intensive activity, which is why we've designed our products with water-efficient technologies, and formed a partnership with non-profit, Made Blue.

Alongside Made Blue, every drop of water saved by an i-mop is mirrored with a donation of clean drinking water in water-vulnerable communities.

This equates to around
18-litres of water
per individual i-mop,
each day around the globe.

So far, this has delivered over
**1 billion litres
of water**
with no signs of slowing down.





cleaning solutions for different industries

No one industry has the same set of cleaning requirements.

Variations to cleaning tools, solutions and processes are required to suit the dynamics of each environment. Your environment may operate 24/7, require morning or night-time cleaning, or may have varying levels of hygiene standards in different areas of the same facility.

i-team is focussed on providing solutions to meet these varied cleaning & hygiene requirements. Our unique 4D cleaning concept approaches cleaning in a different way, ensuring that all 4 dimensions of cleaning are taken care of in a way that is appropriate, no matter the industry.

commercial floor cleaning

imop lite

i-mop xl

i-mop xxl

i-scrub 30

i-scrub 21B

i-remove

i-drive



Allspace

i-mop family

The first of its kind, the patented i-mop combines the flexibility of a floor mop with the power and speed of industrial scrubber drivers.

The i-mop has a revolutionary upright design that offers extraordinary manoeuvrability and breakthrough operational benefits.

The i-mop makes it possible to clean any surface, with freedom of movement and great ease of use. No borders or boundaries.



Full sized scrubber dryer.

This machine isn't just designed for cleaning,
it's designed for the cleaner.

Dual, counter rotating brushes



Twin Brushes

Counter- rotation of twin brushes pushes solution toward center, rather than splashing off to the side of the machine.

Unique Brush Design

Channels that constantly push solution towards – not away from center. Plus, concentrically stepped bristles trap fluid and prevent splashing.

Squeegee System Design

Placement of squeegee under weight of equipment creates pressure against uneven floor surfaces for better fluid recapture.

Squeegee Location

Location of squeegee immediately behind brushes (vs. behind wheels) retrieves fluid before its fans out to sides.

Extreme mobility

Low profile deck lets you clean underneath cabinets and ledges.
Brushes clean right up to the edge.
Clean small and confined spaces with ease.
Unlimited mobility with a foldable scrub deck & transport wheels, light enough to pick up.



Incredible manoeuvrability

360 degree handle, never bin easier.
Take tight corners with ease.
Clean where even an auto-scrubber can't go thanks to the tight turning radius

- take me for a spin
360° with ease



Join the revolution

a smarter way of cleaning

Interested in an i-mop for your business?

Great choice! The i-mop family cleans up to 70% faster than conventional wet mopping, and up to 30% faster than conventional auto scrubbing.

The i-mop and it's ability to get right to the edge and under obstacles results in maximum maneuverability. With 3 smart models and a range of pads & brushes it's guaranteed that there's 1 that fits your needs.



available in 3 sizes

imop Lite



i-mop XL



i-mop XXL



choosing i-mop

| | imop Lite | i-mop XL | i-mop XXL |
|----------------------------------|---|--|---|
| Technical performance | 1400 m ² | 1800 m ² | 2300 m ² |
| Practical performance | 700-1000 m ² | 1000-1300 m ² | 1200-1800 m ² |
| Types of rooms | <ul style="list-style-type: none"> - Multi-level rooms - Route cleaning - Multiple locations - Small rooms with obstacles | <ul style="list-style-type: none"> - Small and mid-sized rooms with obstacles | <ul style="list-style-type: none"> - Mid-sized and large open rooms - Long aisles |
| Weight without battery and water | 11,5 kg | 18,5 kg | 21 kg |
| Weight with battery and water | 13 kg | 22,5 kg | 32 kg |

imop lite

Compact scrubber dryer

The most compact device in the i-mop family, the i-mop lite excels at home or work, providing effortless cleaning of small to medium spaces.

Scrub width 37 cm

Extreme mobility

Patented design, ideal for cleaning floors in areas where you cannot normally use a scrubber.



Exceptional power

High-speed 500rpm brushes for an intense clean.

Suits all floors

Array of brushes and pads available to suit stone, tiles, concrete and wood floors.



Easy to use

Simple, easy to understand push button controls.

Eco-mode

Activate eco-mode to save additional water, or on moisture sensitive floors.

Light & portable

14kg design fits in the back of a standard car.



Battery operated

Utilises portable lithium-ion batteries, eliminating trip hazards from power leads.

Technical Specifications

| | |
|-------------------------|------------------------------|
| Theoretical performance | 1400 m ² per hour |
| Clean water tank | 3 L |
| Recovery clean tank | 5 L |
| Brush speed | 500 RPM |
| Scrub width | 37 cm |
| Brush pressure | 13.2 kg |
| Battery | i-power 12 Lite |
| Runtime | 45 min |
| Charge time | 6 hours |































Scan for more info

Why imop lite?

- > Extremely manoeuvrable, user-friendly design
- > Dirt removal rating of 97% compared to traditional mopping methods of only 30-40%
- > 3-4 times faster than mopping
- > No more dirty edges – scrubs right to the edge
- > No trip hazards – runs on portable lithium batteries
- > Powerful cleaning on all hard floor surfaces

imop lite accessories

| | CODE | PRODUCT | DESCRIPTION |
|---|---------------------|------------------------------------|--|
|  | IMOPLT.FCT.1100C | imop lite | imop Lite includes charger, battery & blue brushes |
|  | K.1.S.115.0142.0 | i-charge for imop lite | imop Lite battery charger |
|  | K.1.S.115.0143.0 | i-power for imop lite | imop Lite battery |
|  | K.1.S.107.0001.0 | i-store | Heavy duty free standing steel cabinet to store an i-mop and accessories |
|  | K.2.S.115.1054.70 | Soft blue brush (set 2) | Light duty cleaning for timber and delicate floors |
|  | K.2.S.115.1054.797 | Med blue brush (set 2) | Everyday cleaning and scrubbing |
|  | K.2.S.115.1054.1 | Hard red brush (set 2) | Deep cleaning including grout lines |
|  | K.2.S.115.1054.592 | Natural hair brush (set 2) | For timber sports halls and cork floors |
|  | K.2.S.115.1056.797 | Pad drivers (set 2) | Suits all color cleaning pads |
|  | K.20.115.1057.2 | White cleaning pads (set 2) | Light buffing & polishing |
|  | K.20.115.1057.1 | Red cleaning pads (set 2) | Regular buffing & cleaning pad |
|  | K.20.115.1057.79 | Blue med/hd cleaning pads (set 2) | Heavy cleaning pad, dull or unsealed floors |
|  | K.20.115.1057.64 | Green hd cleaning pads (set 2) | Aggressive scrubbing pad & unsealed floors |
|  | K.20.115.1057.0 | Black stripping pads (set 2) | Very aggressive scrubbing & stripping |
|  | K.2.115.1060.64 | Twister green (set 2) | Daily cleaning on stone, concrete, ceramic, vinyl, timber & rubber floors |
|  | K.2.115.1058.1 | Red brush locker (set 2) | HACCP color coded allows for segregation of brushes & tanks for different areas. |
|  | K.2.115.1058.67 | Green brush locker (set 2) | |
|  | K.2.115.1058.797 | Blue brush locker (set 2) | |
|  | K.2.115.1058.8 | Yellow brush locker (set 2) | |
|  | K.1.S.115.0062.357 | Kit assy squeegee | Complete squeegee kit |
|  | K.1.S.115.0214.0 | Kit assy splash guard (set 2) | Splash guard assembly |
|  | K.10.115.0065.0 | Primothane squeegee rubber (front) | High performance squeegee rubber |
|  | K.10.115.0066.0 | Primothane squeegee rubber (rear) | |
|  | K.3.S. 115.0075.357 | Castor wheels (3) | Replacement castor wheels |
|  | K.1.S.115.0089.0 | Recovery tank | Replacement recovery water tank |
|  | K.1.S.115.0079.0B | Clean tank | Replacement clean water tank |
|  | K.1.S.115.1079.2 | Clean tank with i-dose | Replacement clean water tank with i-dose |
|  | K.1.72.0324.0 | Cleaning brush | Cleaning brush for i-mop dirt tank |



i-mop XL

Flexible, effective and fast!

The i-mop is a revolutionary floor cleaning machine that has changed cleaning standards and redefined the concept of a floor scrubber.

Scrub width 46 cm



i-dose cleaning efficiency

Save time and stop wastage by using the i-dose chemical system.



Battery operated

Runs on Lithium batteries like the i-power 12 or 14 batteries that is easily exchangeable when recharging.

Extreme mobility

Low profile deck to clean underneath objects and 360 degrees of flexibility.



2 models to choose from
PLUS | PRO

| | Plus | Pro |
|-----------------------------|------|-----|
| Timer display | ✓ | ✓ |
| Antibacterial recovery tank | ✓ | ✓ |
| Drive support | ✓ | ✓ |
| Park position | ✓ | ✓ |
| i-dose® tank (clean) | ✓ | ✓ |
| i-link | - | ✓ |
| Lift kit | - | ✓ |
| Anti-corrosion coating | - | ✓ |



Click on / click off

Easy to fill, clean & empty and use different tanks for different chemicals.



Extreme cleaning power

With 350 rpm brushes and 22kg of scrubbing pressure the i-mop xl has 96% more cleaning power than a 50cm walk behind floor scrubber.

Easy transport

It comes with wheels for transport, folds up for storage and is compact enough to store in a cupboard anywhere.

Technical Specifications

| | XL |
|-------------------------|---|
| Theoretical performance | 1800 m2 per hour |
| Clean water tank | 4 L |
| Recovery clean tank | 6 L |
| Brush speed | 350 RPM |
| Scrub width | 46 cm |
| Brush pressure | 22.5 kg |
| Batteries | 2 x i-power 12 or 14 |
| Runtime | 90-100 min with i-power 14 140 min with i-power 20 |
| Charge time: i-charge 9 | 90-100 min for i-power 14 120 min for i-power 20 |



Scan for more info


Why i-mop XL?

- > Extremely manoeuvrable scrubber dryer.
- > Dirt removal rating of 97% compared to traditional mopping methods of only 30-40%.
- > 30mins with a mop & bucket will take 5mins with an i-mop.
- > No more tide marks – cleans right to the edge.
- > No trip hazards – runs on portable Lithium batteries
- > 80% lighter than a comparable walk behind scrubber.
- > Applications include timber, vinyl, tiles, natural stone, concrete and more.



Because you save the planet

Water used to clean 300 m²
→




i-mop does not cost it PAYS!

If you feel like dancing, take me for a spin around the floor.



Because you save time

Time needed to clean 300 m²
→



i-mop XXL

Flexible, effective and fast!

The i-mop is a revolutionary floor cleaning machine that has changed cleaning standards and redefined the concept of a floor scrubber.

Scrub width 62 cm



i-dose cleaning efficiency

Save time and stop wastage by using the i-dose chemical system.



Battery operated

Runs on Lithium batteries like the i-power 14 or 20 batteries that is easily exchangeable when recharging.

Extreme mobility

Low profile deck to clean underneath objects and 360 degrees of flexibility.



i-mop XXL PRO

| | |
|-----------------------------|---|
| Timer display | ✓ |
| Anti-corrosion coating | ✓ |
| Drive support | ✓ |
| Parking position | ✓ |
| i-dose® tank (clean) | ✓ |
| i-link | ✓ |
| Lift kit | ✓ |
| Antibacterial recovery tank | ✓ |
| Compatible with i-scent pod | ✓ |
| Detachable vacuum motor | ✓ |
| EPA filter | ✓ |



Click on / click off

Easy to fill, clean & empty and use different tanks for different chemicals.



Extreme cleaning power

With 350 rpm brushes and 32kg of scrubbing pressure the i-mop XXL has 96% more cleaning power than a 50cm walk behind floor scrubber.

Easy transport

It comes with wheels for transport, folds up for storage and is compact enough to store in a cupboard anywhere.

Technical Specifications

| | XXL |
|-------------------------|--|
| Theoretical performance | 2300 m ² per hour |
| Clean water tank | 5 L |
| Recovery clean tank | 8 L |
| Brush speed | 350 RPM |
| Scrub width | 62 cm |
| Brush pressure | 32 kg |
| Batteries | 2 x i-power 14 or 20 |
| Runtime | 60-70 min with i-power 14 130 min with i-power 20 |
| Charge time: i-charge 9 | 90-100 min for i-power 14 120 min for i-power 20 |



Scan for more info

Why i-mop XXL?

- > Extremely manoeuvrable scrubber dryer.
- > Dirt removal rating of 97% compared to traditional mopping methods of only 30-40%.
- > 30mins with a mop & bucket will take 5mins with an i-mop.
- > No more tide marks – cleans right to the edge.
- > No trip hazards – runs on portable Lithium batteries
- > 80% lighter than a comparable walk behind scrubber.
- > Applications include timber, vinyl, tiles, natural stone, concrete and more.



Faster

75% faster than mop & bucket

30% faster than standard box machine

90% reduction of hand cleaning even in obstructed areas



Greener

90% less water and chemicals vs. mop & bucket

30-40% less water and chemicals vs. traditional box machine

75% less plastic waste, with i-dose system

i-mop XXL Pro leaves floors dry in **30 seconds**.

A wet mop takes over **6 minutes!**




Cleaner

90% cleaner than manual hand mopping in hard to reach areas, counters, cash registers and after spillage

30% cleaner than traditional machines, due to higher cleaning power index

Water usage for cleaning 100 m²



Safer

Safer to the cleaner: touchless cleaning,

Safer to customer, cleans and dries floor in less than 30 sec.

Safer to store ambience, with antibacterial tanks



Better

Better for everyone

Better for the user – better ergonomics

Better for store management – less space required, less risk of damage and accidents, machines available 24/7= safety and savings 24/7























Better for the business – less investment, less energy consumption, less costs = better for bottom line

Interchangeable batteries allows 24/7 operation, no downtime







i-mop xl & xxl accessories

| | i-mop xl | i-mop xxl | Name | Description |
|---|---------------------|---------------------|--|---|
|  | K.1.IMOPXLP.FCT.7A | - | i-mop xl plus | i-mop xl plus with blue brushes (No batteries or charger included) |
| | K.1.IMOPXLU.FCT.0A | - | i-mop xl pro | i-mop xl pro with blue brushes (No batteries or charger included) |
| | - | K.1.IMOPXXLU.FCT.0A | i-mop xxl pro | i-mop xxl pro with blue brushes (No batteries or charger included) |
|  | K.1.S.72.0074.2BMZ2 | | i-power 12 - blue (left) | 12ah li-ion batteries Run Time: 75 - 85 min in i-mop xl & 55-65 min in i-mop xxl |
| | K.1.S.72.0079.2BMZ2 | | i-power 12 - grey (right) | |
|  | K.1. S.72.0074.357 | | i-power 14 - blue (left) | 14ah li-ion batteries Run Time: 90-100 min in i-mop xl & 60-70 min in i-mop xxl |
| | K.1. S.72.0079.357 | | i-power 14 - grey (right) | |
|  | K.1. S.72.0074.797 | | i-power 20 - blue (left) | 20ah li-ion batteries Run Time: 140 min in i-mop xl & 130 min in i-mop xxl |
| | K.1.S.72.0079.797 | | i-power 20 - grey (right) | |
|  | K.1.S.72.0344.0 | | i-charge 9 Fast charger | Charge time: 60-70 min for i-power 12, 90-100 min for i-power 14 & 120 min for i-power 20 |
|  | K.2.S.72.0092.70 | K.2.S.72.1092.70 | Soft light blue bristle brush (set 2) | Light cleaning on timber & delicate floors |
|  | K.2.S.72.0092.797 | K.2.S.72.1092.797 | Medium blue bristle brush (set 2) | Everyday scrubbing & cleaning |
|  | K.2.S.72.0092.1 | K.2.S.72.1092.1 | Hard red bristle brush (set 2) | Heavy cleaning & unpolished floors |
|  | K.2.S.72.0342.797 | K.2.S.72.1342.797 | Natural hair bristle brush (set 2) | Rubber floors, cork floors and timber sports halls |
|  | K.2.S.72.0214.797 | K.2.S.72.1214.797 | Pad drives (set 2) | For use with i-mop floor pads |
|  | K.2.S.72.0391.797 | K.2.S.72.1391.797 | Low-density bristle brush blue (set 2) | Medium brush used on sensitive surfaces |
|  | K.2.S.72.0391.1 | K.2.S.72.1391.1 | Low-density bristle brush red (set 2) | Hard brush used on sensitive surfaces |
|  | K.2.S.72.0213.2 | K.2.S.72.1213.2 | White pads (set 2) | Light buffing & polishing |
|  | K.2.S.72.0213.1 | K.2.S.72.1213.1 | Red pads (set 2) | Regular buffing & cleaning |
|  | K.2.S.72.0213.79 | K.2.S.72.1213.79 | Blue pads (set 2) | Heavy cleaning of dull or unsealed floors |
|  | K.2.S.72.0213.64 | K.2.S.72.1213.64 | Green pads (set 2) | Aggressive scrubbing & cleaning unsealed floors |
|  | K.2.S.72.0213.0 | K.2.S.72.1213.0 | Black pads (set 2) | Very aggressive scrubbing & stripping |
|  | K.2.S.72.0216.64 | K.2.S.72.1216.64 | Green twister pads (set 2) | Daily cleaning on stone, concrete, ceramic, vinyl, timber & rubber floors |
|  | K.2.S.72.0216.111 | - | Pink twister pads (set 2) | Daily cleaning (high traffic) on stone, ceramic, vinyl, timber & rubber floors |
|  | K.2.S.72.0216.8 | K.2.S.72.1216.8 | Yellow twister pads (set 2) | Daily cleaning & renovation on stone, ceramic, vinyl, timber & rubber floors |
|  | K.2.S.72.0216.4 | K.2.S.72.1216.4 | Orange twister pads (set 2) | Cleaning non-homogenous ceramic tiles & renovation of terrazzo, stone & concrete floors |
|  | K.2.S.72.0345.0 | K.2.S.72.1345.0 | Melamine pads (set 2) | Daily and deep cleaning of tiles, linoleum, stone & concrete floors |

| | i-mop xl | i-mop xxl | Name | Description |
|---|---------------------|---------------------|---|--|
|  | S.107.0001.10 | | i-store | Heavy duty freestanding steel cabinet to store i-mop & accessories |
|  | IS.I-V.0000A | | i-wall | Wall mount bracket to keep i-mop in place |
|  | IS.I-V.0000B | | i-stand | Heavy duty freestanding holder to keep i-mop in place |
|  | K.2.72.0093.797 | | Blue brush locker (set 2) | For colour coding. Attaches to i-mop brushes or pad drives. |
|  | K.2. 72.0093.1 | | Red brush locker (set 2) | |
|  | K.2. 72.0093.67 | | Green brush locker (set 2) | |
|  | K.2. 72.0093.8 | | Yellow brush locker (set 2) | |
|  | S.72.0251.797 | | Blue cap for clean tank | Haccp color coded caps replace the standard clean water tank caps |
|  | S.72.0251.1 | | Red cap for clean tank | |
|  | S.72.0251.67 | | Green cap for clean tank | |
|  | S.72.0251.8 | | Yellow cap for clean tank | |
|  | K.10.72.0099.2 | K.10.72.1099.2 | Linatex squeegee rubber (front) | High quality standard squeegee rubber - durable & chemical resistant |
|  | K.10.72.0100.2 | K.10.72.1100.2 | Linatex squeegee rubber (rear) | |
|  | K.10.72.0099.3 | K.10.72.1099.3 | Primothane squeegee rubber (front) | Ultimate high performance squeegee rubber - best for oily floors |
|  | K.10.72.0100.3 | K.10.72.1100.3 | Primothane squeegee rubber (rear) | |
|  | K.1.S.72.0401.3 | K.1.S.72.1401.3 | Splash guards (left and right) | Splash guard assembly |
|  | K.1.S.72.0371.0 | K.1.S.72.1371.0 | Scrub bracket | Lift kit for squeegee for deep wet scrubbing & stripping |
|  | K.3.S. 72.0238.32 | | Standard castor wheels (3) | Regular castor wheels for smooth floors |
|  | K.3.S. 72.0238.2S | | Stainless steel castor wheels (3) | Heavy duty stainless steel wheels for longer life on very rough floors |
|  | K.1.S.72.0088.4 | K.1.S.72.1088.4 | Recovery tank | Replacement recovery water tank |
|  | K.1.S.72.0081.797FH | K.1.S.72.1081.797FH | Clean tank (not compatible with i-dose) | Replacement clean water tank |
|  | K.1.72.0324.0 | | Cleaning brush | Cleaning brush for i-mop dirt tank |



Use i-mop XL & XXL with i-dose. See page 71 for more information.

| | i-mop xl & xxl | | Name | Description |
|---|---------------------------|-----------------|----------------------------|--------------------------------------|
|  | K.1.S.72.0081.2 | K.1.S.72.1081.2 | Clean tank with i-dose | Compatible with the i-mop XL & XXL |
|  | K.120.72.0444.111 | | Pink i-dose pods (120pcs) | ID.3 Daily floor cleaner (10ml) |
|  | K.120.72.0444.6 | | Green i-dose pods (120pcs) | ID.7 Degreasing floor cleaner (10ml) |
|  | K.120.72.0444.7 | | Blue i-dose pods (120pcs) | ID.5 Daily floor cleaner (10ml) |

i-dose concept

Ultimate efficiency

If there's a better way to do it, we find it.
Say farewell to standard cleaning detergents and the inefficiency of walking back and forth for refills.
The i-dose cleaning pods are here to revolutionize your cleaning.



ID.5 Daily floor cleaner

Mild but effective daily use hard floor cleaner. Dislodges soils commonly found on most floor surfaces without leaving residue that can promote resoilage or create slippery conditions.



ID.3 Sanitary floor cleaner

Safe and mildly acidic cleaner. Suitable for most hard floor substrates and grout, especially designed to remove organic soils, soap scum, calcium, limescale and other soils commonly found on restroom floors.



ID.7 Degreasing floor cleaner

Degreasing floor cleaner. Suitable for all hard floor substrates. Especially effective in removing animal and vegetable-based grease from foodservice environments, and petroleum-based grease from automotive, industrial and retail environments.



Perfect dosing.
Everytime.

- ✓ imop Lite
- ✓ i-mop XL
- ✓ i-mop XXL

i-link it's in the cloud


Manage your assets It's not just about cleaning

While cleaning has never been more important, we believe effective cleaning is more than 'just' the removal of soil. It means ensuring the health and safety of people, while making the job easier, simpler, more efficient, and even fun. It means consistent results all over the world, while protecting the world.

i-link gives you an online overview of all your assets (on the go): tools, machines and compliances. You could instantly see how machines are used, how they perform and where they're located.

Get in the cloud Link your inventory

From now on, i-link® will be integrated in the (new) imop Lite, i-mop XL (PRO), XXL (PRO); i-drive, and i-sense (PRO). **More machines will follow in 2023.**



You can see all your assets details and even create service tickets on your mobile app, manage them online, and share the tickets with suppliers.



One place
for all your tools,
machines and
compliances



i-scrub 30

Powerful orbital scrubber

The i-scrub 30EM Pro is a single disc scrubbing machine offering extreme cleaning power on both carpet and hard floors, thanks to its innovative scrubbing technology. Choose between cable or battery.

Solution tank

Apply solution as you scrub for additional cleaning power.

Lightweight

Easy single-person lift; say goodbye to heavy 30kg traditional scrubbers.

Edge protection

Soft rubber edge allows cleaning close to furniture without risk of damage.

Multi-surface cleaning

Includes soft & hard brushes and microfibre pads for carpet & hard surface scrubbing.

Soft grips

Soft handles for superb control and excellent user ergonomics.

Battery

Compatible with i-power 12 & i-power 14

Revolutionary cleaning power

Unique orbital action scrubs the floor with 1650 cleaning passes per minute.



Easy transport

Folding wheels make it easy to take the i-scrub 30EM Pro with you everywhere you go. When the wheels are hindering your work, simply fold them away.

Technical Specifications

| | 30 EM Pro (cable) | 30 EM Pro B (battery) |
|-----------------------|-------------------|-----------------------|
| Weight | 12.6 kg | 14,4 kg |
| Size (l x w x h) | 27 x 23 x 120 cm | 27 x 23 x 120 cm |
| Power | 650 W | 250 W |
| Brush speed (Orbital) | 1650 RPM | 1650 RPM |
| Scrub width | 30 cm | 30 cm |
| Cable length | 10 m | - |
| Tank capacity | 1.7 L | 1.7 L |
| Battery | - | i-power 12 or 14 |












Scan for more info

Why i-scrub 30EM Pro?

- > Versatile – strip, clean, scrub & buff floors
- > Clean hard floors and carpet
- > Safer - no side swing like swing scrubbers
- > Easy to lift & transport
- > 1650 rpm; up to 8 times the effective cleaning power of traditional single disc machines

i-scrub 30 accessories

| | CODE | PRODUCT | DESCRIPTION |
|---|-------------------|--------------------------------|---|
|  | EM3P,I-V.1110C | i-scrub 30EM Pro | Includes soft & medium brushes, pad drive + white & microfibre pads. Cable-version |
|  | EM3PB,I-V.000B | i-scrub 30EM Pro B | Without battery and charger. Includes soft & medium brushes, pad drive + white & microfibre pads |
|  | K.1.S.28.0010.0 | Soft carpet brush black | Used for light agitation 0,25 mm. |
|  | K.1.S.28.0010.704 | Medium brush blue | Used for general scrubbing 0,40 mm. |
|  | K.1.S.28.0010.1 | Hard brush red | Used for general and heavy scrubbing 0,50 mm. |
|  | K.1.S.28.0010.3 | Hard brush grey | Used for heavy scrubbing 1,0 mm. |
|  | K.1.24.0035.0 | Pad holder | Replacement pad drive |
|  | K.1.24.0036.0 | Polishing pad white | White soft pad for light buffing and polishing |
|  | K.1.24.0037.0 | Microfibre bonnet pad | Absorbent microfibre pad with polypropylene strips for encapsulation cleaning of carpets and rugs |



i-scrub 21B

Battery powered micro-scrubber

Compact, multi-purpose scrubber with maximum cleaning power and operator ergonomics.



Easy to use

Lightweight, ergonomic and easily controlled from the handle grip.

Long run time

Scrub for up to 2.5 hours at a time.

Onboard tank

Dispense cleaning solution right where you need it for accurate cleaning results.

Multi-surface cleaning

Includes soft & hard brushes, pad drives and microfibre pads for upholstery cleaning.

Dual brush head

Twin 400rpm brush heads provide higher mechanical power and effective cleaning for narrow gaps in tight areas.



Hand or pole mount

Complete with pole-mount for floors, or handheld version for walls and elevated areas.



Flexible head

The 360-degree adjustable head offers access to hard-to-reach areas; horizontal and vertical.



Technical Specifications

| | |
|------------------------|-------------|
| Weight | 3.2 kg |
| Runtime | 150 minutes |
| Charge time | 210 minutes |
| Brush speed | 400 RPM |
| Scrub width | 21 cm |
| Minimal clearance area | 95 mm |



















Scan for more info

Why i-scrub 21B?

- > Clean hard to reach, dirty areas
- > Takes the hard work out of cleaning
- > Extreme cleaning power – dual 400rpm brush heads
- > Cleans almost any surface type
- > Adjustable telescopic handle and 360-degree swivel head to adapt to any application
- > Perfect furniture cleaning

i-scrub 21B accessories

| | CODE | PRODUCT | DESCRIPTION |
|---|---------------------|----------------------------------|--|
|  | ES2.I-V.1410C | i-scrub 21B | Complete battery scrubber with telescopic wand including battery, charger & accessories. |
|  | ES2.I-V.1131C | i-scrub 21B handheld | Handheld battery scrubber including battery, charger & accessories |
|  | K.1.S.97.2023.0 | Battery | 14.4 V, 6.6 Ah rechargeable lithium battery |
|  | K.1.S.97.2024.4 | Charger | Battery charger |
|  | K.2.S.97.0702.3/0 | Soft brush black (set 2) | Light agitation of hard and soft surfaces 0,25 mm. |
|  | K.2.S.97.0702.3/704 | Medium brush blue (set 2) | General scrubbing 0,40 mm. |
|  | K.2.S.97.0702.3/22 | Hard brush white (set 2) | Heavy scrubbing 0,60 mm. |
|  | K.2.S.97.0702.3/33 | Hard brush grey (set 2) | Heavy scrubbing 1,0 mm. |
|  | K.2.S.97.0704.3/0 | Pad drives (set 2) | Replacment pad holders |
|  | K.10.97.0703.2 | White scrub pad (10 pcs) | Light buffing & polishing |
|  | K.10.97.0703.1 | Red scrub pad (10 pcs) | Regular buffing & cleaning |
|  | K.10.97.0703.79 | Blue scrub pad (10 pcs) | Medium cleaning pad |
|  | K.10.97.0703.64 | Green scrub pad (10 pcs) | Heavy scrubbing pad |
|  | K.10.97.0703.0 | Black scrub pad (10 pcs) | Very aggressive scrubbing and stripping |
|  | K.10.97.0703.9 | Mixed scrub pad (10 pcs) | Combination of all the scrub pads 2 ea |
|  | K.2.S.97.0705.7 | Microfibre pad (set 2) | Absorbent microfibre pads ideal for upholstery cleaning |



i-remove

Gum & graffiti remover

With i-remove, six-seconds is all it takes to safely dissolve pesky gum and graffiti marks, transforming dirty surfaces before your eyes with precision.

Easy to use

Controls located in the head of the machine.

Safe to use

Works in different environments; no dangerous fumes or heat present.

No waste-water

Low volumes of water, unlike a pressure-cleaner means there is no need to restrict areas to pedestrians, and reduces environmental impact.

6 seconds is all it takes

Eliminate any unwanted sticky materials (chewing gum, stickers, lining glue) in just six-seconds.



Highly portable

Includes trolley handle and integrated backpack harness.

Cord-free operation

Interchangeable lithium-ion batteries eliminates trip hazards.

No residue

i-remove solution dissolves gum, leaving no sticky residue on surfaces.

Suitable for all surfaces

Remove gum & graffiti on hardwood, soft floors, tarmac, doors, cabinets, plywood, concrete and steel.



Technical Specifications

| | |
|-------------------------|--|
| Weight | 9.4 kg |
| Tank capacity | 2.5 L |
| Consumption | 2 L per hour |
| Batteries | 1 or 2 i-power 12 or 14 batteries |
| Run time (2 batteries) | 80 min with i-power 12 & 100 min with i-power 14 |
| Charge time: i-charge 9 | 60-70 min for i-power 12 & 90-100 min for i-power 14 |













Scan for more info

Why i-remove?

- > Fast & effective
- > Stops gum build-up – deal with gum removal as part of regular cleaning routines
- > No trip-hazards – runs on portable lithium batteries
- > Effective on all surfaces
- > Easy to use with low operating weight

i-remove accessories

| | CODE | PRODUCT | DESCRIPTION |
|---|---------------------|---------------------------|--|
|  | IGM.I-V.0000B | i-remove | i-remove without battery & charger |
|  | IGM.I-V.0000M | i-remove mini | i-remove without battery & charger, handheld |
|  | K.1.S.72.0074.2BMZ2 | i-power 12 - blue (left) | 12ah li-ion batteries Run time 1 x battery: 40 min Run time 2 x batteries: 80 min |
|  | K.1.S.72.0079.2BMZ2 | i-power 12 - grey (right) | |
|  | K.1.S.72.0074.357 | i-power 14 - blue (left) | 14ah li-ion batteries Run time 1 x battery: 50 min Run time 2 x batteries: 100 min |
|  | K.1.S.72.0079.357 | i-power 14 - grey (right) | |
|  | K.1.S.72.0344.0 | i-charge 9 Fast charger | Charge time: 60-70 min for i-power 12 & 90-100 min for i-power 14 |
|  | 106.3014.797 | Steel brush | Hard brush for concrete, pavers & bitumen |
|  | 106.3013.797 | Nylon brush | Soft brushes for carpet & matting |
|  | K.12.106.0143.0 | Concentrate solution | 1l eco-solvent aids in gum breakdown and ensures no residue. 1:9 Dilution |



i-drive

The smarter ride-on floor scrubber

A groundbreaking world-first that combines the i-mop lite onboard with a ride-on scrubber, allowing operators to stop and clean small spaces as part of their cleaning routine.



Easy operation

No PhD required to operate the i-drive; we have done all the programming for you. Self-explanatory icons and a clear control panel make this one user-friendly ride.

Small space cleaning

Stop and clean small spaces such as washrooms with the on-board i-mop lite.



Refill on-the-go

Fill, refill and empty the i-mop Lite easily. You're no longer bound to filling stations; simply get fresh water from the i-drive, or empty the recovery tank into the i-drive.

Ramp

Safe and ergonomic loading and unloading of the i-mop lite.



Adjustable pedal

The pedal is easily positioned to meet the driver's exact requirements.



Interchangeable Batteries

Holds 6 x i-power 14 or 20 batteries. With 2 sets of batteries, you can operate it 24/7.

i-stack 3

Recharge our batteries with the included wall mounted charging system.



Technical Specifications

| | |
|----------------------------|--|
| Theoretical performance | 2745 m ² per hour |
| Practical performance | 1400 m ² per hour |
| Pad pressure | 25 kg |
| Pad speed | 175 RPM |
| Typical operational weight | 208 kg |
| Gross vehicle weight | 349 kg |
| Driving speed | 5.5 km/h |
| Solution tank | 58 L |
| Recovery tank | 55 L |
| Detergent tank | 5.5 L |
| Battery | 6 x i-power 14 or 20 |
| Runtime | 80 min with i-power 14 & 120 min with i-power 20 |
| Charge time: i-charge 9 | 90-100 min for i-power 14 & 120 min for i-power 20 |
| Turning circle diameter | 166 cm |
| Dimensions | 146 cm x 60 cm |

















Scan for more info

Why i-drive?

- Class-leading cleaning for both large and small spaces
- 24/7 cleaning maximises machine productivity potential
- Improves cleaning route efficiency; reduces operator walking and manual mopping time
- Highly-maneuvrable cleaning combination
- Optimised operator ergonomics and comfort

i-drive accessories

| | CODE | PRODUCT | DESCRIPTION |
|---|-------------------|----------------------------------|---|
|  | IDR.I-V.1100C | i-drive | i-drive including i-mop lite, 12 x i-power 14 batteries, i-stack 3 & 3 x i-charge 9 |
|  | K.1.72.0074.357 | i-power 14 - blue (left) | 14ah li-ion batteries Run time: 80 min |
|  | K.1.S.72.0079.357 | i-power 14 - grey (right) | |
|  | K.1.S.72.0074.797 | i-power 20 - blue (left) | 20ah li-ion batteries Run time: 120 min |
|  | K.1.S.72.0079.797 | i-power 20- grey (right) | |
|  | K.1.S.72.0344.0 | i-charge 9 fast charger | Charge time: 60-70 min for, 90-100 min for i-power 14 & 120 min for i-power 20 |
|  | K.2.118.0070.0 | Medium brush blue (set 2) | Regular scrubbing brush |
|  | K.2.118.0071.0 | Soft brush white (set 2) | Light cleaning on timber & delicate floors |
|  | K.2.118.0106.0 | Medium brush light brown (set 2) | For textured and rough floors |
|  | K.2.118.0107.0 | Tynex brush (set 2) | Heavy duty aggressive scrubbing brush |
|  | K.2.118.0072.0 | Pad driver (set 2) | For use with 30cm cleaning pads |
|  | K.6.118.0074.0 | Black pads (6 pcs) | Very aggressive scrubbing & stripping |
|  | K.6.118.0074.6 | Green pads (6 pcs) | Aggressive scrubbing & cleaning unsealed floors |
|  | K.6.118.0074.1 | Red pads (6 pcs) | Regular buffing & cleaning |

Campaign package



i-stack 3



i-power 14 (12 pcs)



i-charge 9 (3 pcs)



i-drive + imop Lite

commercial vacuum cleaning

i-vac 5

i-vac 5B

i-vac 6

i-vac 9B

co-botic 1700

i-move 2.5B



i-vac 5

Compact electric vacuum cleaner

Meet the leading compact vacuum that sacrifices no reliability, power or performance. The vac 5 is designed for years of trouble-free, user-friendly vacuuming performance.

Dual-reinforced hose

No compromises on strength with double reinforcement at both ends for ultra-long life.

Durable

No plastic here. Genuine stainless steel 3-piece wand; use 2 or 3 sections for different height operations.

Compact design

Ideal for working in smaller areas and close-to-body carrying.

Illuminated switch

Helps troubleshooting in case of power failures or other technical difficulties.



Stop dust leakage when changing bags.

5 liter bag with lock

Integrated cord wrap

Sturdy, ergonomic main handle doubles as a cord wrap.

Tangle-free cable

Internally glued cable strands to eliminate cable twisting and extend cable life.



Integrated tool holders

Hose & wand plus array of accessories can be stored on the machine.

Technical Specifications

| | |
|--------------|------------------|
| Tool size | 32 mm (standard) |
| Weight | 4.8 kg |
| Capacity | 5 L |
| Sound level | 62 dBA |
| Air flow | 50 L/sec |
| Cable Length | 8 m |





















Scan for more info

Why i-vac 5?

- > Compact & reliable
- > Premium European engineering
- > Ultra-durable construction
- > Low maintenance means lower total cost of ownership
- > Onboard tool holders

i-vac 5 accessories

| | CODE | PRODUCT | | CODE | PRODUCT |
|---|-------------------|---|---|---------------------|------------------------|
|  | C05.DMK.1115C | i-vac 5 electric vacuum Including: telescopic wand, parquet floor tool |  | K.1.PAR.22.9045.610 | Floor tool ergo |
|  | 22.0094.830 | Paper bag (pk 10) |  | K.1.PAR.22.9045.6D | Floor tool Parquet |
|  | 22.0094.831 | Microfibre bag (pk 10) |  | K.1.PAR.22.9045.266 | Floor tool combi RD266 |
|  | K.1.105.0013.0 | Replacement filter (pk 1) |  | K.1.PAR.22.9045.8B | Floor tool D272 |
|  | K.3.22.0034.46 | 3 Piece wand |  | K.1.22.9045.87B | Floor tool TURBO TK270 |
|  | K.1.S.02.1000.797 | Telescopic wand |  | K.1.S.02.0031.5 | Upholstery tool |
|  | K.1.03.0039.17 | 8m cable |  | K.1.S. 02.0032.9 | Crevice tool |
|  | K.1.S.02.0029.74 | Bent elbow piece |  | K.1.S.02.0040.5 | Dusting brush |
|  | K.1.S.220107.2048 | 1.8m replacement hose | | | |
|  | 70.0017.1 | Hose connector | | | |



i-vac 5B

Compact battery vacuum

We believe a battery vacuum shouldn't sacrifice its performance. The vac 5B reaches up to 80% of the suction power of a comparable electric vacuum, offering exceptional results with added portability.

Durable

No plastic here. Genuine stainless steel 3-piece wand; use 2 or 3 sections for different height operations.



Battery operated

Choose from i-power 12 or 14 batteries. Operate continuously with easily interchangeable batteries. Compatible with either left or right batteries.

Integrated tool holders

Hose & wand plus all accessories can be stored on the machine.



Stop dust leakage when changing bags.

5 liter bag with lock

Dual-reinforced hose

No compromises thanks to a double reinforced construction at both ends for ultra-long life.

Powerful suction

Powerful motor reaches 80% (indication) of the suction of cable operated vacuums.

Compact design


Ideal for working in smaller areas and close-to-body carrying.

Illuminated switch

Helps troubleshooting in case of power failures or other technical difficulties.

Technical Specifications

| | |
|-------------------------|--|
| Tool size | 32 mm (standard) |
| Weight | 5.2 kg |
| Capacity | 5 L |
| Sound level | 62 dBA |
| Air flow | 40 L/sec |
| Batteries | 1 x i-power 12 or 14 |
| Battery spec i-power 12 | 24 V 12 Ah |
| Run time | 35 min with i-power 12 & 50 min with i-power 14 |
| Charge time: i-charge 9 | 60-70 min for i-power 12 & 90-100 min for i-power 14 |
























Scan for more info

Why i-vac 5B?

- > Compact & reliable
- > Premium European engineering
- > Choice of batteries & chargers
- > Ultra-durable design means lower total cost of ownership
- > Onboard tool holders

i-vac 5B accessories

| CODE | PRODUCT | CODE | PRODUCT |
|---|---------------------------|---|------------------------|
|  C5B.I-V.0000B | vac 5b battery vacuum |  K.1.S.220107.2048 | 1.8m hose |
|  K.1.S.72.0074.2BMZ2 | i-power 12 - blue (left) |  K.3.22.0034.46 | 3 Piece wand |
|  K.1.S.72.0079.2BMZ2 | i-power 12 - grey (right) |  K.1.S.02.1000.797 | Telescopic wand |
|  K.1.S.72.0079.357 | i-power 14 (left) |  K.1.S.02.0029.74 | Bent elbow piece |
|  K.1.S.72.0074.357 | i-power 14 (right) |  K.1. PAR.22.9045.610 | Floor tool ergo |
|  K.1.S.72.0344.0 | i-charge 9 |  K.1.PAR.22.9045.6D | Floor tool Parquet |
|  105.0013.0 | Paper bag (pk 10) |  K.1.PAR.22.9045.266 | Floor tool combi RD266 |
|  22.0094.831 | Microfibre bag (pk 10) |  K.1.PAR.22.9045.8B | Floor tool D272 |
|  K.1.105.0013.0 | Replacement filter |  K.1.PAR.22.9045.87B | Floor tool TURBO TK270 |
| | |  K.1.S.02.0031.5 | Upholstery tool |
| | |  K.1.02.0032.9 | Crevice tool |
| | |  K.1.S.02.0040.5 | Dusting brush |



i-vac 6

Powerful electric commercial vacuum

The i-vac 6 is a powerful and practical high quality vacuum cleaner, packed with features. This vacuum is built to be indestructible while retaining class-leading suction and high-tech features.

Quiet mode

Choose high-power (62 dBA) or low-power (58 dBA) settings for daytime cleaning.

Resilient body

Virtually indestructible body. All components assembled with screws, instead of rivets.

Dual-reinforced hose

No compromises - double reinforced at both ends for ultra-long life.



Whizzo

Patented Whizzo indicator makes a loud high tone when bag is full, or the vacuum is clogged, preventing motor damage and costly repairs.

Durable

Heavy duty stainless steel extendible wand to suit varying height operators.



Ultra fine, double filtration

Choose from Standard, medical-grade HEPA 14 or even ULPA filtration. Dual filter design - both pre & post-motor- enable the highest possible levels of air quality.

Tangle-free cable

Internally glued cable strands to eliminate cable twisting and extend cable life.



Fragrance cassette

Inbuilt fragrance cassette leaves a pleasant aroma after vacuuming.

Durable wheels

Long-life wheels made of shock absorbing materials.




Why i-vac 6?

- Robust European engineering
- High quality tools & accessories
- Ultra-high filtration performance
- Patented Whizzo technology prevents motor damage
- Optional fragrance cassette
- Offers 3 levels of filtration: Standard, HEPA H14 or ULPA










Technical Specifications















| | |
|--------------|------------------|
| Tool size | 32 mm (standard) |
| Weight | 6.8 kg |
| Cable length | 15 m |
| Capacity | 6 L |
| Air flow | 50 L/sec |



Scan for more info

i-vac 6 accessories

| | CODE | PRODUCT |
|---|-------------------|--|
|  | C06.DMK.11155 | i-vac 6 Including: HEPA-filter telescopic wand, parquet floor tool |
|  | 22.0094.830 | Paper bag (10 bags) |
|  | 22.0094.831 | Microfibre bag (pack 10) |
|  | K.1.S.02.0029.74 | Bent elbow piece |
|  | 70.0017.1 | Hose connector dupro |
|  | K.1.03.0039.15 | 15m cable |
|  | K.1.S.02.1000.797 | Telescopic wand |
|  | K.2.22.0034.41 | 2-Piece wand |
|  | K.1.S.220107.2045 | Hose 2.5m |

| | CODE | PRODUCT |
|---|----------------------|---|
|  | K.1.77.0012.0 | Standard cassette filter black |
|  | K.1.77.0012.1 | HEPA 14 cassette filter red |
|  | K.1.77.0012.701 | ULPA cassette filter blue |
|  | K.1.70.0168.0 | Standard cartridge filter black |
|  | K.1.70.0168.1 | HEPA 14 cartridge filter red |
|  | K.1.70.0168.701 | ULPA cartridge filter blue |
|  | K.1. PAR.22.9045.610 | Floor tool ergo |
|  | K.1.PAR.22.9045.6D | Floor tool Parquet |
|  | K.1.PAR.22.9045.266 | Floor tool combi RD266 |
|  | K.1.PAR.22.9045.8B | Floor tool D272 |
|  | K.1.PAR.22.9045.87B | Floor tool TURBO TK270 |
|  | K.1.02.0032.9 | Crevice tool |
|  | K.1.S.02.0031.5 | Upholstery tool |
|  | K.1.S.02.0040.5 | Dusting brush |

design your own


Change top color, and apply own brand

Supplied with telescopic wand, parquet floor tool and HEPA filter (i-vac 6).

i-vac 5: minimum 36 pcs.

i-vac 6: minimum 20 pcs.

add
your logo



Choose from these top colors



i-vac 9B

High-performance battery vacuum

Say goodbye to power cords and wall sockets and say hello to vacuuming productivity with the vac 9B. The ultra-high performance commercial battery vac.

Ultra fine, double filtration

Choose from Standard, medical grade HEPA 14 or even ULPA filtration. Dual filters (both pre & post-motor) enable the highest possible levels of air quality.

Quiet mode

Choose between high-power (62 dBA) or low-power (58 dBA) settings.



Battery operated

Choose to run off 1 or 2 i-power 12 or 14 batteries. Operate continuously with easily interchangeable batteries.

Resilient body

Virtually indestructible body. All components assembled with screws, instead of rivets.

Dual-reinforced hose

No compromises - double reinforced at both ends for ultra-long life.

Durable

Heavy duty stainless steel extendible wand to suit varying height operators.

Integrated tool holders

Hose & wand plus all accessories can be stored on the machine.



Optional i-brush

Agitates carpet to loosen dirt and dust and improve cleaning performance.

Technical Specifications

| | |
|-------------------------|--|
| Tool size | 32 mm (Standard) |
| Weight | 5.2 kg |
| Capacity | 5 L |
| Airflow | 40 L / sec |
| Runtime (2 batteries) | 80 min with i-power 12 & 100 min with i-power 14 |
| Charge time: i-charge 9 | 60-70 min for i-power 12 & 90-100 min for i-power 14 |





























Scan for more info

Why i-vac 9B?

- > Premium battery powered vacuuming performance
- > Choice of batteries & chargers
- > Ultra durable = lower total cost of ownership
- > On-board tool holders
- > Ultra-high filtration performance
- > Up to 80min run-time with dual i-power 14 batteries

i-vac 9B accessories

| | CODE | PRODUCT | | CODE | PRODUCT |
|---|---------------------|----------------------------|---|---------------------|---------------------------------|
|  | C9B.I-V.0000B | vac 9b |  | K.1.77.0012.0 | Standard cassette filter black |
|  | K.1.S.72.0074.2BMZ2 | i-power 12 - blue (left) |  | K.1.77.0012.1 | HEPA 14 cassette filter red |
|  | K.1.S.72.0079.2BMZ2 | i-power 12 - grey (right) |  | K.1.77.0012.701 | ULPA cassette filter blue |
|  | K.1.S.72.0079.357 | i-power 14 - blue (left) |  | K.1.74.0168.0 | Standard cartridge filter black |
|  | K.1.S.72.0074.357 | i-power 14 - grey (right) |  | K.1.74.0168.1 | HEPA 14 cartridge filter red |
|  | K.1.S.72.0344.0 | i-charge 9 Fast charger |  | K.1.74.0168.701 | ULPA cartridge filter blue |
|  | 22.0094.80 | Paper bags (pack 10) |  | K.1.PAR.22.9045.610 | Floor tool ergo |
|  | 22.0096.0 | Reuseable cloth bag |  | IBH.I-V.0000C | i-brush powerhead |
|  | K.1.S.02.0029.74 | Bent elbow piece |  | K.1.PAR.22.9045.6D | Floor tool Parquet |
|  | K.1.S.02.1000.797 | Telescopic wand |  | K.1.PAR.22.9045.266 | Floor tool combi RD266 |
|  | K.1.S.220107.2045 | 2.5m hose |  | K.1.PAR.22.9045.8B | Floor tool D272 |
| | | |  | K.1.PAR.22.9045.87B | Floor tool TURBO TK270 |
| | | |  | K.1.02.0032.9 | Crevice tool |
| | | |  | K.1.S.02.0031.5 | Upholstery tool |
| | | |  | K.1.S.02.0040.5 | Dusting brush |



co-botic 1700 basic

Commercial robotic vacuum cleaner

The co-botic 1700 is a smart, programmable vacuum robot that allows you to simply sit back and watch the cleaning magic happen before your eyes.

Using the App

Create cleaning plans, exclusion zones and assign it to a schedule for automatic cleaning - all from the i-team professional App.




Remote controlled

Use the remote to directly start autonomously cleaning a room, instead of using the app.



Optional Docking station

The co-botic 1700 automatically finds the route to the docking station, empties itself and recharges while docked.



Sophisticated live mapping

Fitted with 25 advanced sensors to ensure an optimal and efficient cleaning outcome.



Dustbin inside

The removable dust collector is fitted with a HEPA filter to ensure clean exhaust air.



Technical Specifications

| | |
|--------------------------|---------------|
| Power rate | 50 W |
| Voltage | 14.4 V |
| Runtime | 270 minutes |
| Charge time | 240 minutes |
| Sound level | 65-73 dB |
| Speed | 0.3 m/s |
| Dust bin volume | 400 ml |
| Dimensions (l x w x h) | 350x350x98 mm |
| Docking station capacity | 4.2 L |



Scan for more info

Why co-botic 1700?

- > Unleash the efficiency of automated vacuuming
- > Free up staff to focus on other tasks
- > Automatic emptying into docking station
- > Eliminate the strain on operators from Manual vacuuming
- > Program the co-botic 1700 with the app - or allow it to program itself

co-botic 1700 Hotel

Keep it simple with the Hotel Version

The Hotel Version gives you all the same cleaning features as the basic, however this version is more simple.

Use Co-botic 1700 Hotel version in any room, press the start button and it starts to clean the room.

No need for Wifi-access or App, the Hotel versions cleans the entire room and gets right back to the starting point when finished.

Ready to be carried to the next cleaning task.



Trolley Basic

Lets you store and transport six Co-botic 1700.
Charge all machines simply by plugging into the wall.
Charger can be integrated on the trolley.



Why hotel version?

- > Simple Plug & Play concept, press start and let it clean
- > No need for WiFi-access or App
- > Cleans the entire room and stops right where you started it
- > Designed for hotels, classrooms and other areas where you have closed environments
- > Easy to carry to next cleaning task
- > Easily emptied after usage

Did you know?

Co-botic 1700 is using up to 8-10 times less energy compared to cable vacuum cleaners















Scan for more info



Powerful performance
And easy to empty

co-botic accessories

| | CODE | PRODUCT | DESCRIPTION |
|---|--------------------|-----------------------------|---|
|  | COB17N.FCT.0230A | Co-Botic 1700 basic | Smart and programmable vacuum robot. Works with WiFi and app. |
|  | COB17N.FCT.0230A/H | Co-Botic 1700 hotel | Smart vacuum robot. With special software for plug/play use. |
|  | COB17.FCT.0230B | Co-Botic 1700 station | Docking Station for Co-botic 1700 Basic version. |
|  | COB17N.TRL.1100C | Co-Botic 1700 trolley | Trolley on wheels for storage and transport of up to 6 Co-botic 1700 Hotel version and chargers (not included). |
|  | K.3.123.0022.0 | Cloth bag (3 pcs) | Vacuum bag for Docking Station |
|  | S.123.0005.0 | Assy filter | Filter for Co-botic 1700. |
|  | K.1.S.123.0018.0 | Kit assy side brush (2 pcs) | Complete side brush kit. |
|  | 123.0042.2 | Cleaning tool | Cleaning brush. |
|  | 123.0043.996 | Plastic flap | Plastic flap for dust box. |
|  | S.123.0004.2 | Dust box | Dust box. |
|  | S.123.0015.0 | Main brush | Main cleaning brush. |
|  | S.123.0016.2 | Main brush cover | Complete cover for main brush. |


hurtigere renere mere miljørigtig



i-move 2.5B

Cordless backpack vacuum cleaner

Say hello to next generation backpack vacuuming. The i-move 2.5b combines lightweight and ergonomic design with serious vacuuming power and productivity.



Easy to operate

Turn the machine on and off with a remote-control power switch.



Long run time

2 x i-power 8.7 batteries give up to 52 mins of runtime.

Dual-purpose nozzle

The nozzle can be used on both hard and soft floors.



Smarter materials

Extendable hose and handle.

360° Swivel hose

The 360° swivel hose keeps the hose untangled while you clean.

Ergonomic design

The light weight of only 5.28kg (including batteries) makes the i-move 2.5B easy to work with.

Filtration options

Choose between a standard or HEPA 14 filter.

Smells clean, is clean

Optional i-scent fragrance cartridge leaves a pleasant smell in the room after cleaning.

Why i-move 2.5B?

- > Next generation backpack design
- > Premium European engineering
- > High quality tools & accessories
- > Battery operated means no trip hazards
- > i-scent leaves a pleasant smell after cleaning

Technical Specifications

| | |
|-----------------|---|
| Carry Weight | 5.28kg (incl 2 batteries) |
| Body size | 22.4 x 21.4x 47.6 cm |
| Capacity | 2.5 L |
| Sound level | 64 dBA |
| Sealing suction | 14 Kpa |
| Airflow | 30L/sec |
| Batteries | 2 x i-power 8.7 |
| Runtime | 52 min |
| Charge time | 4.3 hours with 2A charger & 1.7 hours with 5A charger |



Scan for more info

Codes

| | |
|--|---|
| i-move 2.5B with 2 batteries & i-charge 5 charger IME25-I-V.1115C | Telescopic wand (530mm) K.1.S.119.0081.0 |
| i-power 8.7 battery S.119.001.3 | Stretch hose 0.5 m K.1.S.02.0024.1/000 |
| i-charge 5 (4 port charger) K1.S.119.0100.9 | Bend 32mm w/t holder K.1.S.119.0080.0 |
| Single charger K1.S.119.0012.4 | Upholstery tool S.02.0031.5 |
| Paper bags (10) K.100.119.0049.0 | Dusting brush S.02.0040.5 |
| Reusable cloth bag (1) 119.0049.1 | Crevice tool 02.0032.9 |
| Standard cassette filter K.1.119.0044.0 | 32mm Gulper Floor Tool PAR.22.9045.610 |
| HEPA 14 cassette filter K.1.119.0044.1 | 32mm Combo Floor Tool PAR.22.9045.266 |
| Air outlet filter K.1.S.119.0062.357 | Fragrance pods (3pcs) K.3.I-SCENT |

surface cleaning

i-spraywash

i-fibre

i-scrub 26H



i-spraywash

Fast foam cleaning system

i-spraywash is a user-friendly, plug & play foam gun with integrated chemical dosing. It uses unique chemical tablets alongside a specialised nozzle that creates an active foam to improve cleaning results and your productivity.

Easy to use

1. Choose your tab
2. Apply foam
3. Let the foam work its magic
4. Rinse

Faster cleaning

The unique spray pattern of the i-spraywash cleans at 1sqm per second.

Integrated dosing

Adjust dosage on the fly with the integrated dosage control.

Faster rinsing

After foaming, disconnect the dosing unit and attach the adjustable rinse nozzle for fast rinsing.

Ergonomic

Weighs just 1kg – less than half the weight of comparable foamers.



Flow adjustment

Adjust pressure on the run as required.

Active foam

Very fine active foam bubbles are lighter and cling for longer on vertical surfaces.

No wastage

Use colour-coded tablet holders to store leftover tablets for next time.

Standard connections

2 Versions available. Gardena (standard garden hose fitting) and Nito (common in food industry). Operates off mains water and normal tap pressure.



Choose the right tab

Choose from 5 tablets for different cleaning and disinfection tasks.

- > Tablet 1 – Descaling
- > Tablet 9 – Daily cleaning
- > Tablet 12 – Heavy, greasy area cleaning
- > DesTab – Disinfection with active oxygen
- > ChlorTab Extra – Disinfection with Chlorine



Technical Specifications

| | |
|------------------------|------------|
| Weight | 0.8 kg |
| Size | 34 x 19 cm |
| Water pressure | 2-4.5 bar |
| Max. using temperature | 45° |
| Min. using temperature | 5° |



Scan for more info


Why i-spraywash?

- > Speeds up cleaning processes – 1sqm per second
- > Lightweight & easy to use
- > Eliminates chemical wastage
- > Superior cleaning & disinfection
- > Reduces water & chemical usage


Foam that **sticks** around

When you apply a thin layer of foam to the wall with the i-spraywash it really sticks. This means less rinsing of heavy airy foam on the floor. This means less water and chemicals give you a much better cleaning result and will save you time and water when rinsing.

Regular foam




Active i-spraywash foam




Regular foam




Active i-spraywash foam





















Regular foam



Active i-spraywash foam



i-spraywash accessories

| | CODE | PRODUCT | DESCRIPTION |
|---|-----------------|---------------------------------------|--|
|  | SPW.SYSTEM.C | Starter kit gardena | Suits standard garden hose fittings |
| | SPW.SYSTEM.N | Starter kit nito | Nito fittings - common in food industry |
|  | SPW.STARTPACK.C | Starter pack w/tablets gardena | i-spraywash gun with 12 mixed boxes of tablets |
|  | SPW.WATERPACK.C | Waterpack starter kit gardena | i-spraywash gun with 10m hd hose & water connections |
|  | SPW.TAB18.1 | Tablet 1 (pk 18) | Acidic cleaner for periodic cleaning. Effective against limescale and good for periodical or regular bathroom cleaning |
|  | SPW.TAB18.9 | Tablet 9 (pk 18) | For daily cleaning of all washable surfaces. Effective against fats, oils and general soiling. |
|  | SPW.TAB18.12 | Tablet 12 (pk 18) | Heavy duty cleaning & degreasing tablet for very dirty conditions. Effective against body fat, oils, grease and heavy dirt |
|  | SPW.TAB18.CH | Chlortab tablet (pk 18) | Most popular disinfection tablet. Active chlorine base |
|  | SPW.TAB18.DE | Destab tablet (pk 18) | Active oxygen based disinfection tablet. Use where chlortab is offensive due to the chlorine odour. |
|  | SPW.TABKIT.3 | Blue tablet holder kit | |
|  | SPW.TABKIT.4 | Red tablet holder kit | |
|  | SPW.TABKIT.5 | White tablet holder kit | Colour-coded tablet holders to store leftover tablets |
|  | SPW.TABKIT.6 | Yellow tablet holder kit | |
|  | SPW.TABKIT.7 | Black tablet holder kit | |
|  | SPW.PART.5 | Disinfection nozzle | Disinfection nozzle with adjust spray |
|  | SPW.WATER.5 | Flexible connector adaptor kit | Flexible connector adaptor kit (1/2, 3/4, 1 inch) |
|  | SPW.WATER.6 | Indoor adapter for water tap | For connecting garden hoses to threaded indoor vanity taps |
|  | SPW.WATER.8 | Water thief | For connecting garden hoses to non threaded taps |
|  | SPW.PART.8 | Foam nozzle | Replacement foam nozzle with filter |

i-scrub 26H

Superior surface cleaning tool

The i-scrub 26h replaces hand cloths and exposes hidden soiling with the inbuilt UV light. Enabling a completely new level of surface wiping productivity and effectiveness.



Rubber grip

Comfortable, ergonomic hand grip for extended cleaning periods. Optional set of 4 grips for colour coding applications.

700 wash guarantee

i-fibre is designed for serious commercial use, lowering the total cost of ownership.



Integrated UV light

Expose stains and residual bacteria invisible to the naked eye.

Inbuilt scraper

Remove tough soil with the inbuilt scraping edge.



Trio-split microfiber pads

Fully colour coded with triple the dirt removal capacity of traditional microfibre.



Soft-edge technology

Dust and clean rounded areas such as sinks and cornices.

Superior cleaning

Clean faster, offers even surface pressure compared to traditional microfibre hand cloths.

Codes

i-scrub 26H UV light
K.1ETL.I-V.1430C

Coloured e-handle grips
(set 4) K.4.IFP.GRIPS

Blue ewave mop 30 cm
ETROWELPADB

Green ewave mop 30 cm
ETROWELPADG

Red ewave mop 30 cm
ETROWELPADR

Yellow ewave mop 30 cm
ETROWELPADY

Technical Specifications

Battery on-board 3.8 V 2.2 Ah rechargeable

Charger type External 110-230-240

Size (l x w x h) 260 x 100 x 90 mm

Material machine ABS797 + PVC

Weight of product 0.32kg

Runtime 8 hours

Power 1 W

Radiant flux 700 nm

View angle 120 degree

Peak wavelength 365 nm



Scan for more info

Why i-scrub 26H?

- > Expose & remove hidden dirt
- > Unique Trio-split technology reduces germs by up to 99%
- > Superior, higher-productivity cleaning
- > Effectively clean rounded areas like sinks and cornices.
- > Empower staff to uphold higher cleaning standards

i-fibre

Trio-split microfibre technology

Up to 3 times the cleaning power of conventional microfibre, plus ultra-long 700 wash lifecycles for lower cost of ownership and improved environmental outcomes.

Why i-fibre?

- Unique trio-split technology reduces germs by up to 99%
- Specialised tools for effective cleaning on all surfaces
- Fully colour-coded for easy identification
- i-fibre offers cleaning up to 50% faster than other microfibre systems.
- Eliminates dust mopping as small particles are captured in the dirt channels



Scan for more info

40cm Floor Cleaning System




ePOCKET mop frame

- Easy to use ergonomic and lightweight mopping system.
- Quick-release system in the frame of the mop offers a complete hands-free cleaning operation.



eWAVE pads

- Double-stitched and guaranteed for a minimum of 700 washes.
- Unique trio-split technology reduces germs by up to 99%.
- Mesh backing for quick pre-treatment saturation time.



Codes

Ewawe Mop 40 cm Blue
EWAVE18PB

Ewawe Mop 40 cm Green
EWAVE18PG

Ewawe Mop 40 cm Red
EWAVE18PR

Ewawe Mop 40 cm Yellow
EWAVE18PY

ePOCKET 40 cm Mop Frame
IFF.I-V.0000C

30cm Surface Cleaning System



i-scrub 26 H

- Replaces hand cloths and exposes hidden soiling with the inbuilt UV light.
- Soft-edge technology contours to curved surfaces such as coving, baths & showers.



eWALL

- Has a 360° swivel plate that converts into a wall and baseboard cleaner.
- Use with eHANDLE handles.



Codes

Ewawe Mop 30 cm Blue
ETROWELPADB

Ewawe Mop 30 cm Green
ETROWELPADG

Ewawe Mop 30 cm Red
ETROWELPADR

Ewawe Mop 30 cm Yellow
ETROWELPADY

i-scrub 26H W/UV Light
K.1ETL.I-V.1430C

eWALL Cleaning Tool
(30 cm) ETF.I-V.0000C

Pre-Treatment System



Pre-treatment system

- o Use either the 13 or 20 L charge bucket as part of your pre-treatment cleaning solution.
- o Includes hermetically sealed lid.
- o Designed for use with i-fibre cloths, 30cm or 40cm cleaning systems.



Codes

13L Charge Bucket
S.92.0018.390

20L Charge Bucket
S.92.0015.390

Handles



eHANDLES

- o Multi-purpose Aluminum telescopic handles that can be used with the ePOCKET mopping system and the eWALL.



Colored eHANDLE grips

- o Optional set of 4 colored grips for colour coding applications.



Codes

eHANDLE (122 cm)
IFP.48

eHANDLE (183 cm)
IFP.72


Colored eHANDLE Grips
(Set 4) K.4.IFP.GRIPS

Cloths




Microfibre cloths

- o Consists of TRIO-Split Microfibre Technology, retaining three-times the dirt.
- o It's also double-stitched ensuring the cloth keep its shape.




eDOUBLE Microfibre cloths

- o 2-in-1 Microfibre cloth with a glass cloth on the one side and a standard cloth on the other.
- o Polytape edge binding and double hexstich construction keeps cloths flat while cleaning.



Microfibre glass cloth

- o Highly absorbent microfibre cloth leaves glass clean and without streak marks.



Codes

300 gm Microfibre Blue Cloth
M CLOTH300B

300 gm Microfibre Green Cloth
M CLOTH300G

300 gm Microfibre Red Cloth
M CLOTH300R

300 gm Microfibre Yellow Cloth
M CLOTH300Y

Microfibre Glass Cloth
M GLASS

Edouble Microfibre Cloth Blue
E DOUBLEB

Edouble Microfibre Cloth Green
E DOUBLEG

Edouble Microfibre Cloth Red
E DOUBLER

Edouble Microfibre Cloth Yellow
E DOUBLEY

Dusting




Flexible dusting wand

- o The flexible microfibre dusting wand reach into those forgotten and hard-to-reach places.
- o Compatible with eHANDLE for high reach dusting.



MSLEEVE

- o Low pile cover for low moisture light dusting and cleaning.



MWAVE

- o Shaggy dusting cover for high volume dry dusting.



Codes

Flexible Duster Dusting
Wand MFLEXWAVE

Sleeve To Suit Flexible
Duster MSLEEVE

Mwave To Suit Flexible
Duster MWAVE

air purification

i-air

i-sense

i-fogger 3.5



i-air Pro

Commercial air purifier

Ultra-low maintenance, high-capacity air purifier utilising medical grade HEPA H14 filters, UV technology and photo-catalytic oxidation to remove **>99.999%** of airborne viruses, bacteria and particulates.

LAN connected

Connect multiple i-airs and control from a PC.

Medical grade filtration

Highest H14 HEPA filtration with large surface area removes 99.999% of particulates at PM1.0 size.

Quiet, powerful fan

Four choices of fan speeds for blowing cleaned air.

Ultra low maintenance

Up to 24-month lifespan for main H14 filter & up to 12-months for carbon pre-filter.

UV kill chamber

Dual UVC & UVA lamps destroy VOCs, microbes and viruses.

** i-air Pro has been found to kill 99.999% of viruses when independently tested on Coronavirus, influenza, and Staphylococcus.*

Carbon Pre-filter

Air passes through the active carbon pre-filter, removing large particles, odours and VOCs.



Use in combination with the **i-sense air quality meter**



Technical Specifications

| | |
|---|--|
| Dimensions | 127x68x33 cm |
| Weight | 72 kg |
| Control panel | 20 character, 4-line LCD display |
| Noise level (4 fan speeds) | 32 - 61 dB |
| Main HEPA 14 filter life | Average up to 24 months, with 24/7 operation |
| PM particle filtration at $\geq 0,3\mu$ (H14) | $\geq 99,999\%$ |
| VOC reduction (TVOC) | $\geq 95-97\%$ |
| Microbiological contamination reduction level | $\geq 99,9\%$ |
| Recommended room size | 50-500 m ² , depending on air contamination level |
| Control via local LAN | Yes, dedicated website |

Codes

i-air
IAIRU.I-V.1100C/2

i-sense Plus
ISNP.I-V.1100C

HEPA 14 filter
IAIR.HEPAH14



Scan for more info

Why i-air Pro?

- > Specialised combination of UVC + photocatalytic oxidation + HEPA H14 filtration + Carbon pre-filter for superior results
- > Main filter offers up to 24-months lifespan with 24/7 use
- > Self-cleaning kill chamber extends filter life and eliminates bacterial build-ups
- > Removes all 3 contaminants: particulates, bacteria and VOCs
- > Combine with i-sense for a complete IAQ monitoring solution

i-sense

Air quality meter

The i-sense is a portable, easy to use Air quality meter that allows you to accurately monitor the quality of the air inside your surroundings to optimise the air that you're breathing.

Simple interface

Easy to understand icons and controls.

Comprehensive monitoring

Monitors 3 common contaminants: CO₂, PM_{2.5} Particulate Matter, and VOC's, as well as temperature & humidity.

Portable

Choice of optional battery or electrically powered units.



Connected Devices

Easily monitor air quality in multiple locations with the I-link platform.



Practical

Monitor air quality from your smartphone.

2 models to choose from
PLUS | PRO


| | Plus | Pro |
|--|------|-----|
| LCD Touchscreen | ✓ | ✓ |
| LED indicator lighting | ✓ | ✓ |
| VOC Measurement | ✓ | ✓ |
| PM _{2.5} Measurement | ✓ | ✓ |
| CO ₂ Measurement | ✓ | ✓ |
| Temperature | ✓ | ✓ |
| Humidity | ✓ | ✓ |
| Historical Graphs (5 days) | ✓ | ✓ |
| Wall power | ✓ | ✓ |
| Battery Power | ✓ | ✓ |
| Analog Clock | ✓ | ✓ |
| i-link built-in 24/7 room monitoring location services custom alerts | | ✓ |

Why i-sense?

- > Make the invisible visible
- > Combine with i-air air purifiers for a comprehensive air quality strategy
- > Be alerted when air quality requires attention
- > Improve patient, staff and visitor wellbeing
- > Choice of models to suit your requirements

Codes

i-sense Plus
ISNP.I-V.1100C



Scan for more info

Technical Specifications

| Model | Plus | Pro |
|---|--|--|
| Body size (L x W x H) mm | 145x130x145 | 145x130x145 |
| Weight (excl. battery) | 0.81 kg | 0.91 kg |
| Weight (incl. battery) | 1.51 kg | 1.61 kg |
| Power source (battery not included): | i-power 8.7 battery or 5V USB-C wall power | i-power 8.7 battery or 5V USB-C wall power |
| VOC measurement range / accuracy (ppb) | 0-1000 ± 75 | 0-1000 ± 75 |
| PM measurement range / accuracy (ppm) | 400-5000 ± 100 | 400-5000 ± 100 |
| CO ₂ measurement range / accuracy (µg/m ³) | 0-600 ± 10% | 0-600 ± 10% |
| Temperature measurement range / accuracy (°C) | -45 - 125 ± 5 | -45 - 125 ± 5 |
| Humidity measurement range / accuracy (%) | 10-100 ± 1 | 10-100 ± 1 |

i-fogger 3.5

High volume backpack fogger

The i-fogger is a practical tool to have during and after the COVID-19 pandemic. It disinfects surfaces and entire spaces quickly. The mobile unit creates and disperses a disinfectant aerosol (mist) that help reduce the number of airborne micro-organisms and viruses.



Excellent ergonomics

The user wears a backpack, allowing complete freedom of movement.



Self-reset switch

This prevents the machine from automatically or unintentionally restarting.

High-volume disinfection

Easily and effectively disinfect locations with heavy-foot-traffic like cinemas, airplanes, trains, busses, shopping malls and more.



Battery operated

Only needs 1 x i-power 12 or 14 battery for 50mins of use.



A nozzle for every job

Interchangeable nozzles can regulate the mist from 20-150 microns droplet size as needed.

Removable tank

Easily fill, clean & empty the 3 L tank at a sink.

Technical Specifications

| | |
|----------------|--|
| Weight | 7.9 kg |
| Dimensions | 20x60x23 cm |
| Tank capacity | 3 L |
| Battery | 1 x i-power 12 or 14 |
| Run time | 40 min with i-power 12 & 50 min with i-power 14 |
| Charge time: | 60-70 min for i-power 12 & 90-100 min for i-power 14 |
| Speed of spray | 175-100ml/minute |
| Hose length | 1.2 m |
| Droplet size | 20-150 um |
| Machine power | 450W |
| Spray distance | 5-6 m |

Codes

| | |
|---|---|
| i-fogger 3.5 (w/o battery) IFG.FCT.0000B | i-power 12 (left) K.1.S.72.0074.2 |
| Clean Tank S.121.0060.0 | i-power 12 (right) K.1.S.72.0079.2 |
| Spray Nozzles W/T Tool (1 set) S.121.0077.357 | i-power 14 (left) K.1.S.72.0074.357 |
| | i-power 14 (right) K.1.S.72.0079.357 |



Scan for more info

Why i-fogger 3.5?

- > High dispersion rate for high-volume disinfection
- > Interchangeable nozzles for different applications
- > Disinfect even those hard-to-reach places
- > Battery-power allows for freedom of movement

#3D Walls & Ceiling

#4D Air

#2D Furniture

#1D Floors

every dimension counts

4D cleaning the **REAL** clean

Our 4D 4 Dimensional approach to cleaning ensures that no area of cleaning is left out, including the areas that may not have been thought of yet.

cleaning equipment & accessories

i-land S

i-land L Pro

i-land L Pro Drive

i-land XL Pro

i-power

i-stack

i-charge

i-matt

i-dose

i-suit

i-store

i-wall

i-stand

i-know



i-land S Pro

The compact cleaning trolley

Transport all your cleaning products & i-mop on one cart, enabling you to service multiple areas without having to go back and refill, in a convenient, compact and versatile design.



Onboard charger

Charge your i-power batteries on the go with the onboard charger.

Storage basket

Store spray bottles or additional small cleaning accessories.

Dusting tool holder

Attach your dusting tool or i-fibre mop to your cleaning trolley for easy accessibility.

Multiple cleaning tasks

Load up your i-mop, microfibre cloths and mops, chemicals, tanks and batteries on this i-land S.

Air tyres

The versatile air-tyred version can be used outside or on uneven surfaces, whilst remaining perfectly suitable for indoor environments.

Reduce travel time

By consolidating all your cleaning tools into the i-land you reduce traveling time back to the storage.

Large Deck

Easily load your i-mop, lock it in position and safely transport it on the large deck space.



Technical Specifications

| | |
|-----------------|------------------|
| Weight | 32 kg |
| Size | 59 x 54 x 113 cm |
| Tyre size | 25 cm |
| Type | Air tyres |
| Equipment slots | 9 |

Codes

i-land s air tyres
ICSP.FCT.0000A



Scan for more info

Why i-land S Pro?

- > Compact & versatile
- > Secure storage for your i-mop, tools and accessories
- > Large pneumatic-tyres for easy transport over rough surfaces, or up stairs
- > Eliminates productivity lost returning to the cleaner's storeroom
- > Carries additional tanks to support colour coded cleaning routines

i-land L Pro

Fully equipped cleaning trolley

When it comes to cleaning large buildings and on-site projects, you need an effective workstation that holds all your cleaning equipment. The i-land L Pro is an outstanding all-in-one solution.

Charge on the go

Integrated power board and charger holders for charging additional i-power batteries while cleaning.

Lockable drawers

Fully enclosed lockable drawers with heavy duty runners for long life.




i-fibre compatible

Designed for use with the i-fibre 4D microfibre cleaning system.



Equipment slots

16 large holders accommodate all your tools and accessories.



Tablet bracket (optional)

The trolley can be fitted with a bracket to hold your iPad or tablet.

Tank storage

Store additional i-mop xl/xxl tanks on board for extended cleaning time.

i-mop storage

Onboard ramp for easy mobilisation of the i-mop floor scrubber.

Why i-land L Pro?

- > Store an array of cleaning equipment and accessories on a single mobile cleaning island
- > Colour-coded tank lids and on-board cleaning buckets enable colour-coded cleaning routines, preventing cross-contamination
- > Eliminate productivity lost from returning to the cleaner's storeroom whilst cleaning
- > Ultra heavy duty rotomoulded construction for long life in commercial environments

Codes

i-land L Pro
ICL.FCT.1100A

Grey compartments
bags (2)
103.0025.0



Scan for more info

Technical Specifications

| | |
|------------------|---|
| Weight | 52.8 kg |
| Size (l x w x h) | 140 x 68 x 110 cm |
| Storage capacity | Top & bottom drawer: 51 x 22 x 32 cm |
| Cable length | 10 m |
| Caster size | 5" (rubber) |
| Equipment slots | 16 |

i-land L Pro Drive

Fully equipped, battery-powered cleaning trolley

Part of the innovative i-land range of cleaning workstations, the i-land L Pro Drive is fitted with an electric motor that takes ease-of-cleaning to a whole new level.



Powered cleaning trolley

Easily controlled from the handle. Integrated safety brake stops trolley as soon as hand is removed from the handle.

Lockable drawers

Fully enclosed lockable drawers with heavy duty runners for long life.


i-fibre compatible

Designed for use with the i-fibre 4D microfibre cleaning system.



Equipment slots

16 large holders accommodate all your tools and accessories.



Tablet bracket (optional)


The trolley can be fitted with a bracket to hold your iPad or tablet.

i-mop storage

Onboard ramp for easy mobilisation of the i-mop floor scrubber.

Tank storage

Store additional i-mop xl/xxl tanks on board for extended cleaning time.



Technical Specifications

| | |
|------------------|--|
| Weight | 84 kg |
| Size (l x w x h) | 140 x 68 x 110 cm |
| Storage capacity | Top & bottom drawer: 51 x 22 x 32 cm |
| Cable length | 10 m |
| Caster size | 5" (rubber) |
| Equipment slots | 16 |
| Max incline | 10° |
| Speed | low: 2.5 km/h, medium: 3.5 km/h high: 4.5 km/h |

Codes

i-land L Pro Drive
ICLD.FCT.1100

Grey compartments
bags (2)
103.0025.0



Scan for more info

Why i-land L Pro Drive?

- > Store an array of cleaning equipment and accessories on one battery-powered cleaning island
- > Colour-coded tank lids and on-board cleaning buckets enable colour-coded cleaning routines, preventing cross-contamination
- > Eliminate productivity lost returning to the cleaner's storeroom whilst cleaning
- > Ultra heavy duty rotomoulded construction for long life in commercial environments

i-land XL Pro

The ultimate cleaning trolley

When it comes to cleaning large buildings and on-site projects, you need an effective workstation that holds all your cleaning equipment. That's why we've created the i-land XL Pro, an all-in-one solution.

Charge on the go

Integrated power board and charger holders for charging additional i-power batteries while cleaning.

Lockable drawers

Fully enclosed lockable drawers with heavy duty runners for long life.



i-fibre compatible

Designed for use with the i-fibre 4D microfibre cleaning system.



Equipment slots

18 large holders accommodate all your tools and accessories.



Tablet bracket (optional)

The trolley can be fitted with a bracket to hold your iPad or tablet.

Tank storage

Store additional i-mop xl/xxl tanks on board for extended cleaning time.

i-mop storage

Onboard ramp for easy mobilisation of your i-mop.

Why i-land XL Pro?

- > Store an array of cleaning equipment and accessories on a single mobile cleaning island.
- > Colour-coded tank lids and on-board cleaning buckets enable colour-coded cleaning routines, preventing cross-contamination.
- > Eliminate productivity lost from returning to the cleaner's storeroom whilst cleaning.
- > Heavy duty construction for ultra-long life

Technical Specifications

| | |
|------------------|---|
| Weight | 84.2 kg |
| Size (l x w x h) | 165 x 68 x 110 cm |
| Storage capacity | Top drawer: 55.5 x 50 x 34 cm Bottom drawer (L): 55 x 13.5 x 18 cm Bottom drawer (R): 55 x 29.5 x 28.5 cm |
| Cable length | 10 m |
| Caster size | 5" (rubber) |
| Equipment slots | 18 |



Scan for more info

Codes

i-land XL Pro
ICXL.FCT.1100A

2 Compartment
Grey Bag
103.0025.0

Tablet bracket
1.103.0115.0A

Front castor
103.0013.0

Rear castor
103.0014.0

Lock & key
103.0015.0

Plug-and-play battery system

Our quick exchange i-power battery system means that our battery powered machines provide an effective and relentless cleaning workforce.



i-power 7 batteries

14.4V – 6.6Ah rechargeable Lithium batteries.



i-power 8.7 batteries

1.44V – 8.7Ah rechargeable Lithium batteries.



i-power 12 batteries

25.2V – 12 Ah rechargeable Lithium batteries.



i-power 12 Lite battery

18V – 12Ah rechargeable Lithium batteries.



i-power 14 batteries

25.2V – 14 Ah rechargeable Lithium batteries.



i-power 20 batteries

25.2V - 20Ah rechargeable Lithium batteries (white batteries).

Technical Specifications

| Machine | Battery | Run Time | Charge time | | | | Configuration |
|----------------|-----------------|---------------|-------------|--------------------|------------|------------|-----------------------|
| | | | i-Charge 9 | i-charge imop Lite | i-charge 7 | i-charge 5 | |
| i-mop lite | i-power 12 Lite | 45min | - | 6 hours | - | - | 1 x battery |
| | i-power 12 | 75 - 85 min | 1h20 min | - | - | - | 1 x pair of batteries |
| i-mop xl | i-power 14 | 90 - 100 min | 1h30 min | - | - | - | 1 x pair of batteries |
| | i-power 20 | 130 - 140 min | 2 hours | - | - | - | 1 x pair of batteries |
| i-mop xxl | i-power 12 | 55 - 65 min | 1h20 min | - | - | - | 1 x pair of batteries |
| | i-power 14 | 60 - 70 min | 1h30 min | - | - | - | 1 x pair of batteries |
| | i-power 20 | 120 - 130 min | 2 hours | - | - | - | 1 x pair of batteries |
| i-remove | i-power 12 | 45 min | 1h20 min | - | - | - | 1 x pair of batteries |
| | i-power 14 | 50 min | 1h30 min | - | - | - | 1 x pair of batteries |
| vac 5B | i-power 12 | 35 min | 1h20 min | - | - | - | 1 x battery |
| | i-power 14 | 40 min | 1h30 min | - | - | - | 1 x battery |
| vac 9B | i-power 12 | 90 min | 1h20min | - | - | - | 1 x pair of batteries |
| | i-power 14 | 100 min | 1h30 min | - | - | - | 1 x pair of batteries |
| i-drive | i-power 14 | 80 min | 1h30 min | - | - | - | 3 x pair of batteries |
| | i-power 20 | 120 min | 2 hours | - | - | - | 3 x pair of batteries |
| i-scrub 21B | i-power 7 | 150 min | - | - | 3t30min | - | 1 x battery |
| | i-power 12 | 160 min | 60-70 min | - | - | - | 1 x battery |
| i-land L drive | i-power 14 | 240 min | 100 min | - | - | - | 1 x battery |
| | i-power 20 | 340 min | 120 min | - | - | - | 1 x battery |
| i-cover 1.0 | i-power 12 | 15 hours | 1h20 min | - | - | - | 1 x battery |
| | i-power 14 | 18 hours | 1h30 min | - | - | - | 1 x battery |
| | i-power 20 | 26 hours | 2 hours | - | - | - | 1 x battery |
| i-fogger 3.5 | i-power 12 | 40 min | 1h20 min | - | - | - | 1 x battery |
| | i-power 14 | 50 min | 1h30 min | - | - | - | 1 x battery |
| i-sense | i-power 8.7 | 85 hours | - | - | - | 120 min | 1 x battery |
| i-move 2.5B | i-power 8.7 | 52 min | - | - | - | 100 min | 1 x pair of batteries |

i-charge

i-power battery charging system

Our i-chargers are made to charge the i-power batteries in a short amount of time.



i-charge 9

Fast Charger for i-power 12, 14 & 20 batteries.



i-charge 5

4 port charger for the i-power 8.7 batteries.



Single charger

Charger for the i-power 7 batteries.



i-charge imop lite

Charger for the i-power 12 Lite battery.

i-stack

Wall charging system

Charging the fleet, straight from the wall

i-stack (3/4/6)

Choose how many levels of chargers you need, and assemble them accordingly. (chargers not included).



Compatible Machines

i-power 7

i-scrub 21B

i-power 8.7

i-sense
i-move 2.5B

i-power 12 Lite

i-mop lite

i-power 12, 14 & 20

i-mop xl
i-mop xxl
vac 5B
vac 9B
i-land L Pro Drive
i-drive
i-cover 1.0
i-fogger 3.5
i-remove

Codes

i-power 7
K.1.S.97.2023.0

i-power 8.7
K.1.S.119.001.3

i-power 12 (left)
K.1.S.72.0074.2BMZ2

i-power 12 (right)
K.1.S.72.0079.2BMZ2

i-power Lite 12
K.1.S.115.0143.0

i-power 14 (left)
K.1.S.72.0074.357

i-power 14 (right)
K.1.S.72.0079.357

i-power 20 (left)
K.1.S.72.0074.797

i-power 20 (right)
K.1.S.72.0079.797

i-stack 1 wall charger
WR1.FCT.0000C

i-stack 3 wall charger
WR3.FCT.1100C

i-stack 4 wall charger
WR4.FCT.1100C

i-stack 6 wall charger
WR6.FCT.1100C

i-charge 9
K.1.S.72.0344.0

i-charge i-power 7 / 8.7
K.1.S.97.2024.6

i-charge 5
K.1.S.119.0100.9



Scan for more info



i-matt

Commercial floor mat

i-matt is a durable, clean-in-place, no-trip floor matting system that improves floor safety and ease of cleaning. Better still, the i-matt does not need to be removed before cleaning - it can be cleaned seamlessly with our innovative i-mop, as though it is part of the main floor.



Total 9m per roll

Comes in a 9m roll of 91.5cm wide x 3 pre-cut sections; an ideal size for entrances and walkways.

Adhesive Technology

Lays flat and stays put with no shifting; easily removed with no residue left behind.

Super Absorbent

Absorbs and spreads out water, so the i-matt dries fast; traps dirt to prevent it from being tracked around the cleaned area. Each 9m roll holds up to 30 litres of water.

Hi-Trac surface

Certified by NFSI to reduce slip and fall claims by up to 90%.

Hard wearing

Withstands daily cleaning, extreme foot and wheeled traffic; lasts up to 12 months.

Easy installation

Easily installed. Connect edges to suit all areas and around corners.

Pre-cut

Smart pre-cut version, easy to install in front of doors, or other small places

Technical Specifications

| | |
|-------------------|---|
| Size | Roll of 3 pre-cut sections, each 91.5 cm x 3 m |
| | Pre-cut 89 cm x 60,5 cm |
| Fluids Absorbed | Oils, Coolants, Solvents & Water |
| Absorbency | up to 30 L per roll |
| Temperature Limit | Surface temperatures from 13°C - 49°C |
| Composition | Absorbent - Polypropylene; Adhesive Backing - Proprietary Adhesive Material |

Codes

i-matt 9m roll
K.3.I-MATT.ROLL

i-matt Pre-cut
K.4.I-MATT/PRE



Scan for more info

Why i-matt?

- > Save 5 minutes every day; no removing and relaying mats before/after cleaning
- > Saves money compared with cost of rental mats
- > Captures water and dirt at the door to keep floors cleaner
- > Lowers environmental impact – no harsh laundering chemicals
- > Safer - stops trips, slips and accidents

i-dose

Chemical Dosing System

The i-dose system is designed specifically for the i-mop xl, combining ecologically-conscious cleaning detergents with a user-friendly pod design.

i-dose solution tank

Conveniently equipped with a side port for refilling water without needing to remove the injector. You can easily click-on and click-off the tank as you're used to.



Interchangeable tank

Replaces the existing tank on any i-mop xl model.

i-dose cleaning pods

Choose the perfect i-dose pod for your needs.



ID.5 Daily Floor Cleaner

The i-dose ID.5 Daily Floor Cleaner is an environmentally friendly, plant-based solution for effective everyday cleaning of any hard floor.



ID.3 Sanitary Floor Cleaner

The i-dose ID.3 Sanitary Floor Cleaner is an environmentally friendly, plant-based and mildly acidic cleaning solution designed to cut through limescale and scum buildup in bathroom areas.



ID.7 Degreasing Floor Cleaner

The i-dose ID.7 Degreasing Floor Cleaner is powerful degreasing floor cleaner designed for kitchen and foodservice environments, as well as industrial workshops.



i-dose injector

The injector is inserted on the top port of the new i-dose solution tank. Place the pod here and close the cap. The injector pierces the cup with exactly the right pressure and the liquid disperses evenly in the solution tank.

i-dose cleaning pod holder

Holds up to 10 i-dose cleaning pod refills, enabling dispensing anywhere. The cleaning pod holder fits on the inside of the solution tank.

Why i-dose?

- > No more risky "glug-glug" manual diluting chemicals
- > Perfectly-measured doses eliminate over- or under-dosing
- > Specifically engineered to disperse through water tank without shaking
- > Entirely plant-based cradle-to-cradle formulas
- > One pod accurately doses one i-mop xl tank



Scan for more info

Codes

imop Lite i-dose tank
K.1.S.115.1079.2

i-mop XL i-dose tank
K.1.S.72.0081.2

i-mop XXL i-dose tank
K.S.72.1081.2

Blue ID.5 10ml pod (120pcs)
K.120.72.0444.7

Pink ID.7 10ml pod (120pcs)
K.120.72.0444.111

Green ID.3 10ml pod (120pcs)
K.120.72.0444.6

i-suit

High-reach window cleaning support

The i-suit eliminates neck strains and pains associated with high-mounted window cleaning, reducing operator effort whilst improving the productivity and efficacy of the cleaning process.




High-pressure washers

Attach your pressure washer high-reach wand to make cleaning vertical surfaces with a high-pressure water blaster a breeze.



i-suit glasses

Unique 90-degree glasses allow you to look straight ahead and see your actions vertically.



One handed cleaning

With the integrated pulley taking the weight, cleaning with one hand is a reality.

Multi-brand compatible

Compatible with all brands of high-reach poles.

Backpack & lance

All the weight of your high-reach window cleaning pole is centred and lifted from the middle- liberating the movement, and reducing neck and back strain while offering better visibility of the area being cleaned.

Codes

| | |
|---|--|
| i-suit i-suit.I-V | Suspension strip S.109.0017.0 |
| Clip-on glasses K.1.S.109.0045.0 | Balancer light (white) S.109.0055.2 |
| Angle-view glasses K.1.S.109.0021.2A | Balancer heavy (blue) S.109.0055.797 |

Technical Specifications

| | |
|-------------------|------------------|
| Weight of product | 3.9 kg |
| Size l x w x h | 125 x 80 x 45 cm |
| Accessories | Glasses included |



Scan for more info

Why i-suit?

- > Takes the strain out of window cleaning
- > Easy-to-use
- > Improves cleaning speed
- > Multi-brand compatible
- > Demonstrates innovation to clients, and duty of care to staff


i-store & i-stand

3 Ways to store your i-mop

Easily pack away your i-mop and accessories with our storage options. Mount it against the wall, stand it upright or store it in a heavy-duty steel cabinet.

i-stand Wall

Wall mount bracket designed to hold your i-mop in place.



i-stand

Heavy-duty freestanding holder designed to hold your i-mop in place.

Stay organised


Adjustable shelves and hooks for brushes, pads and chargers makes it easy to find what you're looking for.

Easy to setup

The steel storage closet is easy to build & set up.

i-store

Store your i-mop, wallchargers, pads, brushes and more in one convenient storage unit.



Built-in power outlet

Charge your i-power batteries straight out of the i-store.

Why i-store & i-stand?

- > All-in-one storage makes it the perfect utilities closet in your storage facility
- > Charge your i-mop batteries directly from the built-in power outlet
- > Makes all your i-mop accessories easily accessible
- > Secure the i-mop in your storeroom with a lockable key
- > Organise your storeroom with our storage options

Technical Specifications

| | |
|----------------|--------------|
| i-store | |
| Weight | 70.5 kg |
| Dimensions | 92x42x210 cm |
| Material | Steel |



Scan for more info

Codes

i-store
S.107.0001

i-stand wall
IS.I-V.00A

i-stand Pro
IS.I-V.0000A

Commercial cleaning measurement tools

Data-driven cleaning; the i-know allows you to prove the effectiveness of your cleaning processes, eliminating guesswork, improving accountability and inspiring confidence.

Why i-know?

- Monitor cleanliness with accurate, real-world data
- Demonstrate new levels of innovation & professionalism
- Perform before and after tests to optimise processes
- Reduce safety risks and improve OH&S outcomes
- Empower staff to uphold cleaning standards

Wheeled suitcase

Present a professional image to clients by transporting all i-know testing tools in one sleek, sturdy case.

pH Tester

Test the pH of cleaning solutions, ensuring suitability for delicate surfaces.

Gloss meter

Monitor floor conditions and optimise floor cleaning & polishing processes with the gloss meter.

ATP tests

Use ATP tests to check if surfaces meet expected cleaning standards.

Slip-tester

Slip-alert saves time, money and helps to prevent injuries from slip accidents.



Technical specifications

ATP Meter

| | |
|-------------------------------|--|
| Carry weight | approx 260 grams |
| Size body (l x w x h) | 72 x 191 x 32 mm |
| Operating temp. range | 5 ~ 40° C |
| Relative humidity range | 20 ~ 85%, non condensing |
| Measurement range | 0 to 9999 RLUs |
| Measurement time | 15 sec |
| Measurement noise | +/- 5% or +/- 5RLUs |
| Programmable result threshold | 100 programs |
| Result memory size | 500 tests |
| Batteries size | AA LR6 or E91 |
| Battery types | nom. 1.5V Alkaline (non rechargeable) nom. 1.2V NiMH or NiCD (rechargeable) |
| Charger type | Off-board |
| Battery capacity | min. 6 months (standby mode at 20° C) min. 500 test (continuous reading) |

Gloss Meter

| | |
|-----------------------|--|
| Carry weight | approx 350 grams |
| Size body (l x w x h) | 160 x 75 x 90 mm |
| Operation temperature | 0~40° C |
| Humidity | <85% relative humidity |
| Measuring time | 0.5 sec |
| Measurement angle | 20°/60°/85° |
| Measurement area | 20°: 10 x 10 mm 60°: 9 x 15mm 85°: 5 x 36 mm |

i-alert

| | |
|-----------------------|--------------------|
| Weight slip alert | 5 kg |
| Size body (l x w x h) | 250 x 180 x 70 mm |
| Size ramp | 900 x 190 x 250 mm |

Codes

i-know kit
IKW.I-V.0000C



Scan for more info



partner network

Global Reach - Local Experts

i-team is a global family of distribution partners in over 60 countries. The i-team community is all about sharing; we believe sharing knowledge is critical for creating sustainable solutions.



INQUIRE. INNOVATE. INSPIRE



Phone +45 5079 2020 | hej@i-teamdanmark.dk | www.i-teamdanmark.dk
